



Pass and Seymour
PlugTail® Single Pole Illuminated Decorator Switch 20 amp, Ivory
Part No. PT2625I



PlugTail Registered Single-Pole Illuminated Decorator Switch 20A

Features & Benefits

Ground wire pre-mounted to the box

Mud ring factory installed

4" square x 1 1/2" or 2 1/8" metal boxes

PlugTail Right Angle Connectors with 12 AWG copper pigtails

All Double Gang Kits contain two right angle PlugTail connectors

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	2625I
Color	Ivory	Finish	Matte
UPC Number	785007001228	Country Of Origin	Mexico
Material	Thermoplastic	Features	Decorator Style, Locator Light
Number of Switches	1	Application Sector	Commercial, Industrial
Wall Plate Included	No	Standard	UL 20
Warranty Type	1-Year Limited Warranty	Type	Decorator, Switch

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Connection Location	Back Only	Terminal Accommodation	#14 AWG - #12 AWG
Number of Gangs	1	Throw Type	Single Throw
Amperage	20 A	Number of Poles	Single Pole
Requires Neutral Wire	No	Indoor/Outdoor	Indoor
Mounting Type	Wall Box	Wire Connection Type	PlugTail
Voltage	120.0 V		