



Pass and Seymour  
**PlugTail® 20A 125V Industrial Extra Heavy Duty Spec-Grade Duplex Receptacle, Ivory**  
Part No. PT5362AI



PlugTail Registered Industrial Extra Heavy-Duty Spec Grade Receptacles, 20A, 125V PlugTail Registered devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

## Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

Illuminated face indicates power to receptacle and makes it easy to identify receptacle in dark applications.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Crimped and welded contacts.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Large brass contacts snugly terminate on device blade terminals.

Auto-ground clip assures positive ground.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.  
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only

## Specifications

### General Info

|                       |                |                    |                                          |
|-----------------------|----------------|--------------------|------------------------------------------|
| Product Line          | Pass & Seymour | Color              | Ivory                                    |
| UPC Number            | 785007860337   | Country Of Origin  | Mexico                                   |
| Number of Receptacles | 2              | Features           | Single Piece Plated Steel Mounting Strap |
| Outlet Type           | Straight Blade | Application Sector | Commercial, Industrial                   |

|                                       |                         |                          |                          |
|---------------------------------------|-------------------------|--------------------------|--------------------------|
| Wall Plate Included                   | No                      | Standard                 | cULus UL498, FEDSPEC     |
| Warranty Type                         | 1-Year Limited Warranty |                          |                          |
| Dimensions                            |                         |                          |                          |
| Product Width US                      | 1.625 in                | Product Depth US         | 0.86 in                  |
| Product Height US                     | 2.75 in                 |                          |                          |
| Listing Agencies / 3rd Party Agencies |                         |                          |                          |
| cULus ListingNumber                   | E140596                 | cULus Listed             | Yes                      |
| Technical Information                 |                         |                          |                          |
| Operating Temperature Min             | -40 °C                  | Dielectric Strength      | Withstands 2000V minimum |
| Connection Location                   | Back Only               | Number of Wires          | 3                        |
| Operating Temperature Max             | 60 °C                   | Amperage                 | 20 A                     |
| Number of Poles                       | Double Pole             | Wire Size                | 12 AWG                   |
| Indoor/Outdoor                        | Indoor                  | NEMA Configuration Code  | 5-20R                    |
| Operating Temperature                 | -40°-60°C               | Wire Connection Type     | PlugTail                 |
| Voltage                               | 125.0 V                 | Environmental Conditions | Flammability: UL94 V2    |