



Pass and Seymour
PlugTail® Isolated Ground Spec Grade Receptacles, 15A, 125V, Orange
Part No. PTIG5262



PlugTail Registered Isolated Ground Spec Grade Receptacles, 15A, 125A

Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

No exposed terminals create a finger safe application before, during, and after installation.

Crimped and welded contacts.

Large brass contacts snugly terminate on device blade terminals.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Plated steel wrap strap design for maximum durability and corrosion resistance.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Orange
UPC Number	785007307603	Country Of Origin	Mexico
Number of Receptacles	2	Features	Isolated Ground, Single Piece Plated Steel Mounting Strap
Outlet Type	Straight Blade	Application Sector	Commercial
Wall Plate Included	No	Standard	UL 498, FEDSPEC

Warranty Type	1-Year Limited Warranty		
Dimensions			
Product Width US	1.5 in	Product Depth US	0.625 in
Product Height US	2.75 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E140596	cULus Listed	Yes
Technical Information			
Operating Temperature Min	-40 °C	Connection Location	Back Only
Phase	Three	Number of Wires	3
Operating Temperature Max	60 °C	Amperage	15 A
Number of Poles	Double Pole	Wire Size	12 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-15R
Operating Temperature	-40°-60°C	Wire Connection Type	PlugTail
Voltage	125.0 V		