



Pass and Seymour
PlugTail® Connectors, Right Angle, Solid, 6-in
Part No. PTR6SOL



PlugTail Registered Connectors, Right Angle, Solid, 6-inch PlugTail Registered devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

Features & Benefits

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtailed.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Plated steel wrap strap design for maximum durability and corrosion resistance.

Available in any wire length up to 25 inches, use Configurable Solutions to order.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid, for use with PlugTail Receptacles only

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Matte	UPC Number	785007044553
Country Of Origin	China	Features	Plug-In
Application Sector	Commercial	Standard	cULus UL498
Warranty Type	1-Year Limited Warranty	Type	Accessory

Dimensions

Product Length US	6.0 in
-------------------	--------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E140596	cULus Listed	Yes
---------------------	---------	--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Is Tamper-Resistant	Yes
---------------------	--------------------------	---------------------	-----

Connection Location	Back Only	Number of Wires	3
---------------------	-----------	-----------------	---

Wire Size	12 AWG	Indoor/Outdoor	Indoor
-----------	--------	----------------	--------

Wire Connection Type	PlugTail
----------------------	----------