



Pass and Seymour
15A 125V Recessed Tamper-Resistant Duplex Receptacle, White
Part No. R885TRWCC6



Recessed Duplex Tamper-Resistant Outlet. Great for Flat Screen TV's, Furniture pinch points, Kitchen Counters and more. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Recessed Duplex Tamper-Resistant Outlet	Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.
Appliance plugs remain recessed behind wall surface	Great for Flat Screen TV's, Furniture pinch points, Kitchen Counters and more
Tamper-Resistant meets NEC code	Integral wall plate

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007031140
Country Of Origin	China	Number of Receptacles	2
Features	Decorator Style, Recessed	Outlet Type	Straight Blade, Tamper-Resistant
Application Sector	Hospitality, Residential	Wall Plate Included	No
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	2.9 in	Product Weight US	29.986 lb
------------------	--------	-------------------	-----------

Product Volume US	0.18 cu in	Product Height US	4.7 in
Product Length US	2.2 in		

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Is Tamper-Resistant	Yes	Connection Location	Back and Side
Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor
NEMA Configuration Code	5-15R	Wire Connection Type	Internal Pressure Plates, Screw Terminals
Voltage	120.0 V, 125.0 V		