



radiant Collection
Discontinued - radiant® 120V, 1100W Incandescent Single Pole/3-Way Dimmer, Tri-Color
Part No. RH1103PTCCCV6



Upgrade your space with precise dimming control and exceptional style. This dimmer from the radiant Registered Collection is optimized for use with incandescent bulbs and fixtures. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately.

Features & Benefits

For use with incandescent bulbs and fixtures on typical residential (and light commercial) wiring. Usable in both single-pole and 3-way applications. Low-profile paddle switch offers smoother On/Off control, while a separate, ergonomic slider allows you to adjust light levels with precision.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark. Constant memory features returns lights to their previous level after a power failure or outage.

Features durable, high-impact resistant thermoplastic construction. More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	RHCL453PTCCCV6
Color	Ivory, Light Almond, White	Finish	Matte
UPC Number	785007053753	Country Of Origin	China
Material	Steel, Thermoplastic	Features	Color Change Kit, Locator Light, Low-End Trim (Dim Range)
Switch Type	Paddle, Slider	Number of Switches	1
Application Sector	Multi-Dwelling Unit, Residential	Warranty Type	Limited Lifetime Warranty

Type	Dimmer		
Dimensions			
Product Width US	1.75 in	Product Depth US	1.25 in
Product Height US	4.25 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E95219	cULus Listed	Yes
Technical Information			
Preset	Yes	Load Rating	120V 1100W (Halogen), 120V 1100W (Incandescent)
Dimming Compatibility	Forward Phase	Frequency Rating	60 Hz
Number of Poles	3-Way, Single Pole	Wire Size	#14 - #12 AWG
Requires Neutral Wire	No	Indoor/Outdoor	Indoor
Mounting Type	Wall Box	Wire Connection Type	Screw Terminals
Voltage	120 VAC	Load Type	Halogen, Incandescent