



radiant Collection
Discontinued - radiant® Incandescent 700W Dimmer, Dark Bronze
Part No. RH703PDBCCV4



Upgrade your space with precise dimming control and exceptional style. This dimmer from the radiant Registered Collection is optimized for use with incandescent bulbs and fixtures. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately.

Features & Benefits

For use with incandescent bulbs and fixtures on typical residential (and light commercial) wiring. Usable in both single-pole and 3-way applications. Low-profile paddle switch offers smoother On/Off control, while a separate, ergonomic slider allows you to adjust light levels with precision.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark. Constant memory features returns lights to their previous level after a power failure or outage.

Features durable, high-impact resistant thermoplastic construction. More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection. Screw pressure plate back wire allows easier installation and fit into the wall box

Eliminates the need to derate LED bulbs when in multi-gang situations For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	RHCL453PDBCCV4
Color	Dark Bronze	Finish	Metallic
UPC Number	785007053722	Country Of Origin	China
Switch Type	Paddle	Number of Switches	1
Application Sector	Residential	Standard	cULus, CSA Listed, UL 1472

Warranty Type	Limited Lifetime Warranty	Type	Dimmer
---------------	---------------------------	------	--------

Dimensions

Product Width US	1.75 in	Product Depth US	1.25 in
Product Height US	4.25 in		

Technical Information

Compatibility	Incandescent Load	Connection	Screw-down terminals
Number of Gangs	1	Amperage	15 A
Bulb Compatibility	Incandescent	Number of Poles	3-Way, Single Pole
Wire Size	#14 - #10 AWG	Indoor/Outdoor	Indoor
Wattage	700 W	Mounting Type	Box
Supply Voltage	120 VAC	Voltage	120.0 V
Environmental Conditions	95% (relative humidity, non-condensing)		