



radiant Collection
radiant® Single Pole/3-Way Fan Speed Control, Tri-Color
Part No. RHDH163PTCCCV6



Upgrade your fan control with the sweet sound of silence. Specially designed to virtually eliminate the fan motor "hum." This device provides quieter fan speed control while featuring the sleek, clean lines of radiant Registered for a sophisticated touch. This fan control switch handles a max load of 1.6A. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately.

Features & Benefits

Designed to virtually eliminate the motor's hum for quieter use.

Offers installation flexibility, working in both single-pole and 3-way applications.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Installs easily in place of a standard light or fan control switch. Rated for a max load of 1.6A.

Returns the fan to its previous level after a power failure.

More color options available to fit any style.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory, Light Almond, White
Finish	Satin	UPC Number	785007053692
Country Of Origin	China	Material	Steel, Thermoplastic
Features	3-Speed Fan Control, Color Change Kit, De-Hummer Fan Control, Locator Light	Switch Type	Paddle, Slider
Number of Switches	1	Application Sector	Multi-Dwelling Unit, Residential
Warranty Type	Limited Lifetime Warranty	Type	Fan Speed Control

Dimensions

Product Width US	1.75 in	Product Depth US	1.25 in
Product Height US	4.25 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E109655	cULus Listed	Yes
---------------------	---------	--------------	-----

Technical Information

Preset	Yes	Load Rating	120V 1.6A (FAN MOTOR)
Dimming Compatibility	Fan Speed Only	Frequency Rating	60 Hz
Number of Poles	3-Way, Single Pole	Wire Size	#14 - #10 AWG
Requires Neutral Wire	No	Indoor/Outdoor	Indoor
Mounting Type	Wall Box	Wire Connection Type	Flying Leads
Voltage	120 VAC	Load Type	AC Fan Motor