



radiant Collection
radiant® LED/CFL Dimmer, White
Part No. RHL743PW



Upgrade your space with precise dimming control and exceptional style. This dimmer from the radiant Registered Collection is optimized for use with LED bulbs and fixtures compliant with the SSL 7A standard for energy efficiency. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately.

Features & Benefits

SSL 7A - Compliant, this dimmer is for use with LED bulbs and fixtures also designed to the SSL 7A standard for efficiency. For use in both single-pole and 3-way applications.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

No derating* required for 2-gang applications. * Reducing the maximum wattage a dimmer can handle. This is sometimes required for multi-gang applications.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Low-profile paddle switch offers smoother On/Off control, while a separate, ergonomic slider allows you to adjust light levels with precision.

Constant memory features returns lights to their previous level after a power failure or outage.

Features durable, high-impact resistant thermoplastic construction.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Satin	UPC Number	785007133882
Country Of Origin	China	Material	Steel, Thermoplastic
Features	Color Change Kit, High-End Trim (Dim Range), Locator Light, Low-End Trim (Dim Range)	Switch Type	Paddle, Slider
Number of Switches	1	Application Sector	Residential

Standard	CSA Listed, cULus, UL Listed	Warranty Type	Limited Lifetime Warranty
Type	Dimmer		
Dimensions			
Product Width US	1.29 in	Product Depth US	1.0 in
Product Height US	3.18 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E95219	cULus Listed	Yes
Technical Information			
Preset	Yes	Load Rating	120V 450W (CFL), 120V 450W (LED), 120V 700W (Halogen), 120V 700W (Incandescent)
Dimming Compatibility	Forward Phase	Frequency Rating	60 Hz
Maximum Humidity	95% (relative humidity, non-condensing)	Number of Poles	Single Pole 3-Way
Wire Size	#14 - #10 AWG	Requires Neutral Wire	Yes
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Wire Connection Type	Screw Terminals	Voltage	120 VAC
Load Type	CFL, Halogen, Incandescent, LED	Environmental Conditions	Humidity: Less than 95% non condensing