



radiant Collection
radiant® 120V, 1100VA Magnetic Low-Voltage Single Pole/3-Way Dimmer, White
Part No. RHLV1103PW



Upgrade your space with precise dimming control and exceptional style, while saving energy and extending bulb life by reducing the amount of electricity required to power the lights. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately.

Features & Benefits

Low-profile paddle switch offers smoother On/Off control, while a separate, ergonomic slider allows you to adjust light levels with precision.

Usable in both single-pole and 3-way applications.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

Constant memory features returns lights to their previous level after a power failure or outage.

Features durable, high-impact resistant thermoplastic construction.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Satin	UPC Number	785007053302
Country Of Origin	China	Material	Steel, Thermoplastic
Features	Color Change Kit, Locator Light, Low-End Trim (Dim Range)	Switch Type	Paddle, Slider
Number of Switches	1	Application Sector	Residential
Standard	CSA Listed, cULus, UL Listed	Warranty Type	Limited Lifetime Warranty

Type	Dimmer		
Dimensions			
Product Width US	2.5 in	Product Depth US	1.25 in
Product Height US	4.25 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E95219	cULus Listed	Yes
Technical Information			
Preset	Yes	Load Rating	120V 1100VA (MLV - Halogen), 120V 1100VA (MLV - Incandescent)
Dimming Compatibility	Forward Phase	Frequency Rating	60 Hz
Maximum Humidity	95% (relative humidity, non-condensing)	Number of Poles	Single Pole 3-Way
Wire Size	#14 - #10 AWG	Requires Neutral Wire	No
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Wire Connection Type	Screw Terminals	Voltage	120 VAC
Load Type	Halogen, Incandescent	Environmental Conditions	Humidity: Less than 95% non condensing