



radiant Collection  
radiant® 4-Button Digital Timer, Nickel  
Part No. RT2NICCV4



Installs easily in place of a standard light or fan switch, or older spring-wound timer and includes manual on/off through the paddle switch for added convenience. A locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately.

## Features & Benefits

Works with a variety of light bulbs or fixtures, including: Incandescent, LED, fluorescent, compact fluorescent (CFL), magnetic low-voltage (MLV) and electronic low-voltage (ELV), 1/6 hp.

Automates control of lights for energy and cost savings. Also includes manual on/off through the paddle switch for added convenience.

Lets you select a desired preset shut-off time, including 60, 40, 20 and 10 minutes.

Installs easily in place of a standard light or fan switch, or older spring-wound timer.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

More color options available to fit any style.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

## Specifications

### General Info

|                     |                         |                    |                         |
|---------------------|-------------------------|--------------------|-------------------------|
| Product Line        | Pass & Seymour          | Color              | Nickel                  |
| Finish              | Metallic                | UPC Number         | 785007158380            |
| Country Of Origin   | China                   | Material           | Polycarbonate           |
| Features            | Decorator Style, Timer  | Switch Type        | Paddle                  |
| Number of Switches  | 1                       | Application Sector | Commercial, Residential |
| Wall Plate Included | No                      | Standard           | cULus                   |
| Warranty Type       | 1-Year Limited Warranty | Type               | Switch                  |

Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 1.69 in | Product Depth US | 1.88 in |
| Product Height US | 4.2 in  |                  |         |

Technical Information

|                       |                  |                        |                                                                |
|-----------------------|------------------|------------------------|----------------------------------------------------------------|
| Load Rating           | 15 A @ 120 VAC   | Connection Location    | Back and Side                                                  |
| Horsepower Rating     | 1/6 HP @ 120 VAC | Terminal Accommodation | #14 AWG - #12 AWG                                              |
| Contact Rating        | 600Watts         | Number of Gangs        | 1                                                              |
| Throw Type            | Single Throw     | Number of Buttons      | 4                                                              |
| Amperage              | 15 A             | Number of Poles        | Single Pole                                                    |
| Requires Neutral Wire | Yes              | Indoor/Outdoor         | Indoor                                                         |
| Timing Range          | 10-60 minutes    | Mounting Type          | Wall Box                                                       |
| Location Rating       | Dry              | Wire Connection Type   | Push Wire, Wire Terminal                                       |
| Voltage               | 120.0 V          | Load Type              | CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon |