



radiant Collection
radiant® 4-Button Digital Timer, White
Part No. RT2WCCV4



Installs easily in place of a standard light or fan switch, or older spring-wound timer and includes manual on/off through the paddle switch for added convenience. A locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately.

Features & Benefits

Works with a variety of light bulbs or fixtures, including: Incandescent, LED, fluorescent, compact fluorescent (CFL), magnetic low-voltage (MLV) and electronic low-voltage (ELV), 1/6 hp.

Automates control of lights for energy and cost savings. Also includes manual on/off through the paddle switch for added convenience.

Lets you select a desired preset shut-off time, including 60, 40, 20 and 10 minutes.

Installs easily in place of a standard light or fan switch, or older spring-wound timer.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

More color options available to fit any style.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Satin	UPC Number	785007034387
Country Of Origin	China	Material	Polycarbonate
Features	Decorator Style, Timer	Switch Type	Paddle
Number of Switches	1	Application Sector	Commercial, Residential
Wall Plate Included	No	Warranty Type	1-Year Limited Warranty
Type	Switch		

Dimensions

Product Width US	1.69 in	Product Depth US	1.88 in
Product Height US	4.2 in		

Technical Information

Load Rating	15 A @ 120 VAC	Connection Location	Back and Side
Horsepower Rating	1/6 HP @ 120 VAC	Terminal Accommodation	#14 AWG - #12 AWG
Contact Rating	600Watts	Number of Gangs	1
Throw Type	Single Throw	Number of Buttons	4
Amperage	15 A	Number of Poles	Single Pole
Requires Neutral Wire	Yes	Indoor/Outdoor	Indoor
Timing Range	10-60 minutes	Mounting Type	Wall Box
Location Rating	Dry	Wire Connection Type	Push Wire, Wire Terminal
Voltage	120.0 V	Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon