



Pass and Seymour
Screw Mount, Steel Stud Box with Quick/Click
Part No. S118RS



Single-Gang Steel-Stud Box with Quick/Click and Captive Combo Head Self-Tapping Mounting Screws on Each End. Two Quick/Entries on each end. 100 pack.

Features & Benefits

Quick/Entry: feature speeds installation by eliminating need for tools, allows you to push stripped or unstripped non-metallic cable into a single gang plastic box without removing knockouts.

Can be used for steel, aluminum, or wood studs.

Molded of high-impact thermoplastic.

Quick/Click: feature for fast, easy, secure installations. Cannot cross-thread or strip a mounting screw.

Can be installed on steel studs with most standard crimping tools in addition to CT1 Crimping Tool.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007651713	Country Of Origin	United States
Material	Thermoplastic	Features	Quick Entry, Shallow, Steel Stud Mount
Installation Location	Wall	Number of Knockouts	4
Application Sector	Commercial, Residential	Standard	Residential/Commercial
Warranty Type	1-Year Limited Warranty	Type	Switch & Outlet Boxes

Dimensions

Product Width US	2.25 in	Product Weight US	0.189 lb
------------------	---------	-------------------	----------

Product Volume US	18.0 cu in	Product Depth US	2.719 in
Product Height US	3.75 in	Product Length US	3.75 in
Cubic Capacity	18 in³		

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Number of Gangs	1	Indoor/Outdoor	Indoor
Cable Entry	Back, Bottom, Top	Box Shape	Rectangular
Mounting Type	Screw Mount		