



Pass and Seymour
Steel Stud Bracket Box with Quick/Click
Part No. S122B



Single-Gang Steel Stud BracketBox with Quick/Click, 1/2-inch offset for steel stud mount only. Two stabilizer legs. 100 pack.

Features & Benefits

Quick/Click feature offers fast and dependable installation of devices (single, two, Unique offset tab assures proper alignment three, and four gang). to wall face.

Can be installed on steel studs with most standard crimping tools in addition to CT1 Crimping Tool.

Molded of high-impact thermoplastic.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007301472	Country Of Origin	United States
Material	Thermoplastic	Features	Auto Clamps, Deep, Quick Entry
Installation Location	Wall	Number of Knockouts	4
Application Sector	Commercial, Residential	Standard	UL Listed
Warranty Type	1-Year Limited Warranty	Type	Outlet Box

Dimensions

Product Width US	2.25 in	Product Weight US	0.22 lb
Product Volume US	22.0 cu in	Product Depth US	4.25 in
Product Height US	3.75 in	Product Length US	3.75 in

Cubic Capacity	22 in³		
Technical Information			
Number of Gangs	1	Indoor/Outdoor	Indoor
Cable Entry	Back, Bottom, Top	Box Shape	Rectangular
Mounting Type	Stud Mount		