



Pass and Seymour
Screw Mount Steel Stud Box with Quick/Click
Part No. S235RACS



Double Gang, Screw Mount Steel Stud Box with Captive Combo Head Self-Tapping Mount Screws on Each End. Four Auto/Clamps on Each End. 50 pack.

Features & Benefits

Available in single, single deep, two, three and four gang, and 4 inch round ceiling boxes.	All multi-gang and ceiling boxes include exclusive Auto/Clamp feature.
Single gang include Quick/Entry feature.	Specially designed drill point rapidly penetrates medium gauge steel studs.
Screws have combination Hex/Phillips washer heads.	Quick/Click feature on wall boxes offers fast and dependable installation of devices.
Can be used for steel, aluminum, or wood studs.	Molded of high-impact thermoplastic.
Locator ribs ensure proper alignment on stud and proper offset depth.	

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007652727	Country Of Origin	United States
Material	Thermoplastic	Features	Auto Clamps, Quick Entry
Installation Location	Wall	Number of Knockouts	8
Application Sector	Commercial, Residential	Standard	Residential/Commercial
Warranty Type	1-Year Limited Warranty	Type	Outlet Box

Dimensions

Product Width US	3.969 in	Product Weight US	0.34 lb
Product Volume US	35.0 cu in	Product Depth US	3.375 in
Product Height US	3.969 in	Product Length US	3.969 in
Cubic Capacity	35 in ³		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	143222	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Number of Gangs	2	Indoor/Outdoor	Indoor
Cable Entry	Back, Bottom, Top	Box Shape	Square
Mounting Type	Screw Mount		