



Pass and Seymour
Wood and Steel Stud Bracket Box with Quick/Click
Part No. S354S50AC



Triple Gang, Wood and Steel Stud Bracket Box with Quick/Click. 3/8-inch offset for wood and steel stud mounting. Six Auto/Clamps on each end. For use with 3/8-inch to 5/8-inch wallboard.

Features & Benefits

Available in single, two, three, four gang and 4 inch square boxes.

Single gang include Quick/Entry feature.

Unique offset tab assures proper alignment to wall face.

Can be used for steel, aluminum, or wooden studs.

Molded of high-impact thermoplastic.

Two, three and four gang boxes and 4 inch square include exclusive Auto/Clamp feature.

Quick/Click feature offers fast and dependable installation of devices (single, two, three, and four gang).

Available with 3/8 inch offsets.

Can be installed on steel studs with most standard crimping tools in addition to CT1 Crimping Tool.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007207422	Country Of Origin	United States
Material	Thermoplastic	Features	Auto Clamps, Quick Entry
Installation Location	Wall	Number of Knockouts	12
Application Sector	Commercial, Residential	Standard	UL listed
Warranty Type	1-Year Limited Warranty	Type	Outlet Box

Dimensions

Product Width US	5.781 in	Product Weight US	0.48 lb
Product Volume US	54.0 cu in	Product Depth US	3.0 in
Product Height US	3.75 in	Product Length US	3.75 in
Cubic Capacity	54 in³		

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

Technical Information

Number of Gangs	3	Indoor/Outdoor	Indoor
Cable Entry	Back, Bottom, Top	Box Shape	Rectangular
Mounting Type	Stud Mount		