



Pass and Seymour  
15A 125V Clock Hanger Recessed Single Receptacle with Smooth Wall Plate, White  
Part No. S3713W



Clock Hanger Recessed Receptacle with Smooth Wall Plate 15A, 125V, Gray

## Features & Benefits

Single recessed receptacle. Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

## Specifications

### General Info

|                    |                                              |                       |                         |
|--------------------|----------------------------------------------|-----------------------|-------------------------|
| Product Line       | Pass & Seymour                               | Color                 | White                   |
| Finish             | Matte                                        | UPC Number            | 785007687835            |
| Country Of Origin  | Mexico                                       | Number of Receptacles | 1                       |
| Features           | Recessed                                     | Outlet Type           | Straight Blade          |
| Application Sector | Commercial, Multi-Dwelling Unit, Residential | Wall Plate Included   | Yes                     |
| Standard           | UL 498                                       | Warranty Type         | 1-Year Limited Warranty |

### Dimensions

|                   |          |                  |         |
|-------------------|----------|------------------|---------|
| Product Width US  | 2.74 in  | Product Depth US | 1.88 in |
| Product Height US | 4.478 in |                  |         |

### Listing Agencies / 3rd Party Agencies

|                     |         |              |     |
|---------------------|---------|--------------|-----|
| cULus ListingNumber | E140596 | cULus Listed | Yes |
|---------------------|---------|--------------|-----|

Technical Information

|                 |             |                         |             |
|-----------------|-------------|-------------------------|-------------|
| Number of Wires | 3           | Amperage                | 15 A        |
| Number of Poles | Double Pole | Wire Size               | 14 - 10 AWG |
| Indoor/Outdoor  | Indoor      | NEMA Configuration Code | 5-15R       |
| Voltage         | 125.0 V     |                         |             |