



One Gang Power Outlet Receptacle Opening, 2.156 hole for 2.125 diameter device - 2 mtg. holes, Smooth Metal.

Features & Benefits

Chrome: .040" thick.

70% copper, 30% zinc alloy gives warm, appealing finish to modern decor as well as retrofit applications.

Lacquered to prevent corrosion.

Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze, or galvanized steel.

Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.

Packaged in protective film, with finish-matching screws.

Variety of special plated finishes.

Paintable to match plastic plates.

Can be silk-screened or engraved, and custom punched with over 300 opening styles.

Specifications

General Info

Product Line	Pass & Seymour	Color	Chrome
Finish	Metallic	UPC Number	785007138306
Country Of Origin	United States	Wall Plate Size	Standard Size
Wall Plate Type	Outlet, Round	Application Sector	Commercial, Residential
Warranty Type	1-Year Limited Warranty	Type	Wall Plate

Dimensions

Product Width US	2.75 in	Product Depth US	0.2 in
Product Height US	4.5 in		
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		
Additional Information			
Product Environmental Profile	Yes		
Technical Information			
Thickness	0.04 in	Number of Gangs	1
Indoor/Outdoor	Indoor	Mounting Type	Box Mounted
Orientation	Vertical		