



Pass and Seymour
Screw Mount Steel Stud Box with Quick/Click
Part No. S468RACS



FourGang, Screw Mount Steel Stud Box with captive Combo Head Self-Tapping Mount Screws on Each End. Six Auto/Clamps on Each End. Rear Stabilizing bar virtually eliminates inward movement. 25-Pack.

Features & Benefits

Available in single, single deep, two, three and four gang, and 4 inch round ceiling boxes.

Single gang include Quick/Entry feature.

Screws have combination Hex/Phillips washer heads.

Can be used for steel, aluminum, or wood studs.

Locator ribs ensure proper alignment on stud and proper offset depth.

All multi-gang and ceiling boxes include exclusive Auto/Clamp feature.

Specially designed drill point rapidly penetrates medium gauge steel studs.

Quick/Click feature on wall boxes offers fast and dependable installation of devices.

Molded of high-impact thermoplastic.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007652789	Country Of Origin	United States
Material	Thermoplastic	Features	Auto Clamps, Quick Entry
Installation Location	Wall	Number of Knockouts	12
Application Sector	Commercial, Residential	Standard	Residential/Commercial
Warranty Type	1-Year Limited Warranty	Type	Outlet Box

Dimensions

Product Width US	7.813 in	Product Weight US	0.28 lb
Product Volume US	68.0 cu in	Product Depth US	3.0 in
Product Height US	3.813 in	Product Length US	3.813 in
Cubic Capacity	68 in ³		

Additional Information

Product Environmental Profile Yes

Technical Information

Number of Gangs	4	Indoor/Outdoor	Indoor
Cable Entry	Back, Bottom, Top	Box Shape	Rectangular
Mounting Type	Screw Mount		