



Pass and Seymour  
Wood and Steel Stud Bracket Box with Quick/Click  
Part No. S468S50AC



FourGang, Wood and Steel Stud Bracket Box with Quick/Click. 3/8-inch offset for wood and steel stud mounting. Rear stabilizing bar virtually eliminates inward movement. Six Auto/Clamps at each end. For use with 3/8-inch to 5/8-inch wallboard. 25-Pack.

## Features & Benefits

Available in single, two, three, four gang and 4 inch square boxes.

Single gang include Quick/Entry feature.

Unique offset tab assures proper alignment to wall face.

Can be used for steel, aluminum, or wooden studs.

Molded of high-impact thermoplastic.

Two, three and four gang boxes and 4 inch square include exclusive Auto/Clamp feature.

Quick/Click feature offers fast and dependable installation of devices (single, two, three, and four gang).

Available with 3/8 inch offsets.

Can be installed on steel studs with most standard crimping tools in addition to CT1 Crimping Tool.

## Specifications

### General Info

|                       |                         |                     |                          |
|-----------------------|-------------------------|---------------------|--------------------------|
| Product Line          | Pass & Seymour          | Color               | Gray                     |
| UPC Number            | 785007652796            | Country Of Origin   | United States            |
| Material              | Thermoplastic           | Features            | Auto Clamps, Quick Entry |
| Installation Location | Wall                    | Number of Knockouts | 12                       |
| Application Sector    | Commercial, Residential | Standard            | UL listed                |
| Warranty Type         | 1-Year Limited Warranty | Type                | Outlet Box               |

Dimensions

|                   |            |                   |         |
|-------------------|------------|-------------------|---------|
| Product Width US  | 7.813 in   | Product Weight US | 0.29 lb |
| Product Volume US | 68.0 cu in | Product Depth US  | 3.0 in  |
| Product Height US | 3.75 in    | Product Length US | 3.75 in |
| Cubic Capacity    | 68 in³     |                   |         |

Additional Information

|                |     |                               |     |
|----------------|-----|-------------------------------|-----|
| RoHS Compliant | Yes | Product Environmental Profile | Yes |
|----------------|-----|-------------------------------|-----|

Technical Information

|                 |                   |                |             |
|-----------------|-------------------|----------------|-------------|
| Number of Gangs | 4                 | Indoor/Outdoor | Indoor      |
| Cable Entry     | Back, Bottom, Top | Box Shape      | Rectangular |
| Mounting Type   | Stud Mount        |                |             |