



Pass and Seymour
1 Gang SS Smooth Power Outlet SS720
Part No. SS720



1-Gang Single Power Outlet Receptacle, Round 1.59-inch Opening,
302/304 Stainless Steel

Features & Benefits

Type 302/304 Stainless Steel, non-magnetic: .032" nominal thickness.

High Impact resistant nylon face.

This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion.

Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.

Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.

Packaged in protective film, with finish-matching screws.

Paintable to match plastic plates.

Can be silk-screened or engraved, and custom punched with over 300 opening styles.

Specifications

General Info

Product Line	Pass & Seymour	Color	Stainless Steel
Finish	Metallic	UPC Number	785007129618
Country Of Origin	United States	Wall Plate Type	Outlet, Round
Application Sector	Commercial, Residential	Standard	CSA
Type	Wall Plate		

Dimensions

Product Width US	2.75 in	Product Depth US	0.2 in
------------------	---------	------------------	--------

Product Height US	4.5 in
-------------------	--------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	143223	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Cutout	Power Outlet	Thickness	0.032 in
Number of Gangs	1	Indoor/Outdoor	Indoor
Orientation	Vertical		