



High-profile Brass Cover, fits any floor finish - including carpeting, linoleum, tile floors includes 885 15A, 125A Decorator Duplex receptacle and will accept any decorator device. Cover includes captive screws to prevent loss. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Tamper-Resistant shutters let plugs in, keep other things out.

Standard Decorator opening that accepts GFCI, TVSS, DataCom, or other Decorator devices.

Meets UL514(c) scrub water exclusion test.

Simple mounting box, fits into a 4 3/4 inch hole and mounts with 3 screws included.

UL and cUL Listed. Captive screws on TM1542 Series -- screws will not be lost -- new.

Durable construction, impact, and scratch resistant PVC construction.

Auto/Clamps and knockouts on both sides of box.

Threaded device mounting holes.

Ready for low-voltage wiring, drill guides on underside of cover.

Made in USA.

Specifications

General Info

Product Line	Pass & Seymour	Color	Brass
UPC Number	785007013085	Country Of Origin	United States
Material	Brass	Cover Type	Tamper-Resistant
Features	Durable, Hinged Cover	Application Sector	Commercial, Residential
Standard	UL listed	Type	Floor Box cover

Dimensions

Product Width US	6.5 in	Product Weight US	2.058 lb
Product Height US	0.5 in	Product Length US	0.5 in

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes		
Technical Information			
Number of Gangs	1	Indoor/Outdoor	Indoor
Mounting Type	Box Mounted	Box Cover Position	Horizontal, Vertical
Number of Outlets	1		