



Low-Profile Brass Cover requires minimum 3/8-inch hardwood floor thickness. Includes 885 15A, 125A Decorator Duplex receptacle and will accept any decorator device.

Features & Benefits

Tamper-Resistant shutters let plugs in, keep other things out.	Durable construction, impact, and scratch resistant PVC construction.
Standard Decorator opening that accepts GFCI, TVSS, DataCom, or other Decorator devices.	Auto/Clamps and knockouts on both sides of box.
Meets UL514(c) scrub water exclusion test.	Threaded device mounting holes.
Simple mounting box, fits into a 4 3/4 inch hole and mounts with 3 screws included.	Ready for low-voltage wiring, drill guides on underside of cover.
UL and cUL Listed.	Captive screws on TM1542 Series -- screws will not be lost -- new.
Made in USA.	

Specifications

General Info

Product Line	Pass & Seymour	Color	Brass
UPC Number	785007013092	Country Of Origin	United States
Material	Brass	Cover Type	Tamper-Resistant
Features	Durable, Hinged Cover	Application Sector	Commercial, Residential
Standard	UL listed	Type	Floor Box cover

Dimensions

Product Width US	6.5 in	Product Weight US	2.05 lb
Product Height US	0.125 in	Product Length US	0.125 in

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Number of Gangs	1	Indoor/Outdoor	Indoor
Mounting Type	Box Mounted	Box Cover Position	Horizontal, Vertical
Number of Outlets	1		