



Thermoplastic Cover Includes 15A 125A Decorator receptacle, matching detachable and replaceable hinged door threaded device-mounting holes drill guides for low-voltage poke-through holes accepts any Decorator device mounts on carpeting, hardwood, linoleum, tile floors Four mounting/leveling screws. .For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Tamper-Resistant shutters let plugs in, keep other things out.	Hinged door is removable and easily replaceable.
Durable construction, impact, and scratch resistant PVC construction.	Standard Decorator opening that accepts GFCI, TVSS, DataCom, or other Decorator devices.
Auto/Clamps and knockouts on both sides of box.	Meets UL514(c) scrub water exclusion test.
Threaded device mounting holes.	Simple mounting box, fits into a 4 3/4 inch hole and mounts with 3 screws included.
Ready for low-voltage wiring, drill guides on underside of cover.	UL and cUL Listed. Captive screws on TM1542 Series -- screws will not be lost -- new.
Made in USA.	

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007108828	Country Of Origin	United States
Material	Thermoplastic	Cover Type	Tamper-Resistant
Features	Durable, Hinged Cover	Application Sector	Commercial, Residential
Standard	UL Listed	Type	Floor Box cover

Dimensions

Product Width US	4.72 in	Product Weight US	0.63 lb
Product Depth US	4.0 in	Product Height US	5.5 in
Product Length US	5.5 in		

Technical Information

Number of Gangs	1	Indoor/Outdoor	Indoor
Mounting Type	Box Mounted	Box Cover Position	Horizontal, Vertical
Number of Outlets	1		