



Pass and Seymour
15W Hospital Grade USB Outlet, Type A/C, 15A, Tamper-Resistant, White
Part No. TR15HUSBAC6W



15A 125A Hospital Grade Tamper-Resistant Receptacle USB A/C Fast Charging

Features & Benefits

Overall 6A charging capability with smart current-sharing technology to allow for full 3A through a singular Type-C port.

Posted terminal screws and external back-wire pressure plates for more productive and reliable terminations.

Reinforced nylon USB Type-A ports to withstand abuse over the life of the product.

Type-A and Type-C ports carry a minimum rating of 10,000 insertions.

Slim design allows for installation in standard depth wall boxes.

Efficient power supply meets the Department of Energy (DoE) Level VI no-load power requirement of 100mW max for external power supplies.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
UPC Number	785007207897	Country Of Origin	China
Number of Receptacles	2	Features	USB-A Charging, USB-C Charging
Outlet Type	Hospital Grade, Tamper-Resistant, USB-Charging	Application Sector	Commercial, Healthcare
Wall Plate Included	No	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	1.693 in	Product Depth US	1.425 in
------------------	----------	------------------	----------

Product Height US	2.677 in
-------------------	----------

Technical Information

Is Tamper-Resistant	Yes	Connection Location	Side Only
USB Wattage	15 W	USB Amperage	6 A
Number of USBs	2	Number of Wires	3
Number of Gangs	1	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-15R
Wire Connection Type	Screw Terminals	Voltage	125.0 V