



Pass and Seymour  
**15W Spec Grade USB Outlet, Type A/C, 15A, Tamper-Resistant, White**  
Part No. TR15USBAC6W



Combination Tamper-Resistant 15A Duplex Convenience  
Receptacles with two fast charging 6A USB ports Type A and C

## Features & Benefits

- Protects children: patented shutter system helps prevent improper insertion of foreign objects
- Meets National Electrical Code® Tamper Resistant requirement
- Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced.
- It also has our proven SafeLock® Protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected
- High-impact-resistant thermoplastic construction with tri-drive terminal screws

## Specifications

### General Info

|                    |                                              |                       |                                |
|--------------------|----------------------------------------------|-----------------------|--------------------------------|
| Product Line       | Pass & Seymour                               | Color                 | White                          |
| Finish             | Matte                                        | UPC Number            | 785007209754                   |
| Country Of Origin  | Vietnam                                      | Number of Receptacles | 2                              |
| Features           | USB-A Charging, USB-C Charging               | Outlet Type           | Tamper-Resistant, USB-Charging |
| Application Sector | Commercial, Multi-Dwelling Unit, Residential | Wall Plate Included   | No                             |
| Warranty Type      | 1-Year Limited Warranty                      |                       |                                |

### Dimensions

|                   |          |                  |          |
|-------------------|----------|------------------|----------|
| Product Width US  | 1.693 in | Product Depth US | 1.425 in |
| Product Height US | 2.677 in |                  |          |

Technical Information

|                      |                 |                         |             |
|----------------------|-----------------|-------------------------|-------------|
| Is Tamper-Resistant  | Yes             | Connection Location     | Side Only   |
| USB Wattage          | 15 W            | USB Amperage            | 6 A         |
| Number of USBs       | 2               | Number of Wires         | 3           |
| Number of Gangs      | 1               | Amperage                | 15 A        |
| Number of Poles      | Double Pole     | Wire Size               | 14 - 10 AWG |
| Indoor/Outdoor       | Indoor          | NEMA Configuration Code | 5-15R       |
| Wire Connection Type | Screw Terminals | Voltage                 | 125.0 V     |