



Pass and Seymour
15W Spec Grade USB Outlet, Type A/C, 20A, Tamper-Resistant, White
Part No. TR20USBAC6W



20A 125V Tamper-Resistant Receptacle with two 6A USB fast charging ports Type A and C

Features & Benefits

High Impact resistant nylon face.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007215625
Country Of Origin	Vietnam	Number of Receptacles	2
Features	USB-A Charging, USB-C Charging	Outlet Type	Tamper-Resistant, USB-Charging
Application Sector	Commercial, Multi-Dwelling Unit, Residential	Wall Plate Included	No
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	1.693 in	Product Depth US	1.425 in
Product Height US	2.677 in		

Technical Information

Operating Temperature Min	-40 °C	Is Tamper-Resistant	Yes
Connection Location	Side Only	USB Wattage	30 W
USB Amperage	6 A	Frequency Rating	60 Hz
Number of USBs	2	Number of Wires	3
Operating Temperature Max	60 °C	Amperage	20 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-20R
Mounting Type	Box	Operating Temperature	-40°-60°C
Wire Connection Type	Screw Terminals	Voltage	125.0 V