



Tamper-Resistant Decorator Spec Grade Receptacle, Back and Side Wire, 15A, 125V

Features & Benefits

- Dual mechanical shutter system to help prevent insertion of foreign objects.
- AC receptacles available in 15 and 20A, 125V.
- Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.
- High impact-resistant nylon face and thermoplastic back body.
- Back and side wire capability
- For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007034561
Country Of Origin	Mexico	Number of Receptacles	2
Features	Decorator Style, Single Piece Plated Steel Mounting Strap	Outlet Type	Tamper-Resistant
Application Sector	Commercial	Wall Plate Included	No
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	1.37 in	Product Depth US	0.93 in
Product Height US	3.28 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E140596	cULus Listed	Yes
---------------------	---------	--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Connection Location	Back and Side
Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-15R
Wire Connection Type	Screw Terminals	Voltage	125.0 V