



Pass and Seymour
20A 125V Spec-Grade Tamper-Resistant Decorator Duplex Receptacle, Side Wire, White
Part No. TR26342W



Tamper-Resistant Decorator Spec Grade Receptacle, Side Wire Only, 20A, 125V

Features & Benefits

Dual mechanical shutter system to help prevent insertions of foreign objects.

AC receptacles available in 15 and 20A, 125V.

Auto-ground clip assures positive ground.

Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.

Backed-out tri-drive steel terminal screws. Side wire only.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007034929
Country Of Origin	Mexico	Number of Receptacles	2
Features	Decorator Style, Single Piece Plated Steel Mounting Strap	Outlet Type	Tamper-Resistant
Application Sector	Commercial	Wall Plate Included	No
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	1.37 in	Product Depth US	0.93 in
------------------	---------	------------------	---------

Product Height US	3.28 in
-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E140596	cULus Listed	Yes
---------------------	---------	--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Connection Location	Side Only
Number of Wires	3	Amperage	20 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor
NEMA Configuration Code	5-20R	Wire Connection Type	Screw Terminals
Voltage	125.0 V		