



radiant Collection
radiant® Spec Grade 20A Tamper-Resistant Receptacle, Ivory
Part No. TR26352RI



Take a step up from the standard. This tamper-resistant duplex receptacle installs easily for the basic power every space needs, while featuring the sleek, clean lines of radiant Registered for a sophisticated look. 20A outlets are ideal for use with larger appliances and in commercial settings, as well as to meet regional requirements (Chicago, Canada). Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately. Spec-Grade devices are engineered to meet federal specifications for use in commercial installations.

Features & Benefits

Replaces any standard receptacle with ease, in as little as 10 minutes.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Features durable, high-impact resistant thermoplastic construction.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Satin	UPC Number	785007056020
Country Of Origin	Mexico	Number of Receptacles	2
Features	Decorator Style	Outlet Type	Tamper-Resistant
Application Sector	Commercial, Multi-Dwelling Unit, Residential	Wall Plate Included	No
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	1.37 in	Product Depth US	0.93 in
------------------	---------	------------------	---------

Product Height US	3.28 in
-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E140596	cULus Listed	Yes
---------------------	---------	--------------	-----

Technical Information

Operating Temperature Min	-40 °C	Is Tamper-Resistant	Yes
Connection Location	Back and Side	Number of Wires	3
Operating Temperature Max	60 °C	Amperage	20 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor
NEMA Configuration Code	5-20R	Mounting Type	Box
Operating Temperature	-40°-60°C	Wire Connection Type	Internal Pressure Plates
Voltage	125.0 V		