



Tamper-Resistant Heavy-Duty Decorator Spec Grade Single Receptacle, Back and Side Wire, 20A, 125V



## Features & Benefits

|                                                                                                |                                                                                                                                                                                                                               |
|------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Dual mechanical shutter system to help prevent insertion of foreign objects.                   | Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.                                                                                                                                  |
| Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.  | Backed-out tri-drive brass terminal screws for faster installation.                                                                                                                                                           |
| Internal screw-pressure-plate back and side wire capability.                                   | Two back wire holes for additional wiring flexibility.                                                                                                                                                                        |
| .032 inch thick brass triple-wipe power contacts.                                              | Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.                                                                                                                            |
| For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> . | Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact |

## Specifications

### General Info

|                       |                         |                    |                                                  |
|-----------------------|-------------------------|--------------------|--------------------------------------------------|
| Product Line          | Pass & Seymour          | Color              | Gray                                             |
| UPC Number            | 785007004908            | Country Of Origin  | Mexico                                           |
| Number of Receptacles | 1                       | Features           | Decorator Style, Heavy Duty Steel Mounting Strap |
| Outlet Type           | Tamper-Resistant        | Application Sector | Commercial                                       |
| Wall Plate Included   | No                      | Standard           | UL498, CSA C22.2 No. 42                          |
| Warranty Type         | 1-Year Limited Warranty |                    |                                                  |

---

### Dimensions

|                   |          |                  |          |
|-------------------|----------|------------------|----------|
| Product Width US  | 1.322 in | Product Depth US | 1.188 in |
| Product Height US | 2.635 in |                  |          |

---

### Listing Agencies / 3rd Party Agencies

|                     |         |              |     |
|---------------------|---------|--------------|-----|
| cULus ListingNumber | E140596 | cULus Listed | Yes |
|---------------------|---------|--------------|-----|

---

### Technical Information

|                           |                          |                           |                          |
|---------------------------|--------------------------|---------------------------|--------------------------|
| Operating Temperature Min | -40 °C                   | Dielectric Strength       | Withstands 2000V minimum |
| Is Tamper-Resistant       | Yes                      | Connection Location       | Back and Side            |
| Number of Wires           | 3                        | Operating Temperature Max | 60 °C                    |
| Amperage                  | 20 A                     | Number of Poles           | Double Pole              |
| Wire Size                 | 14 - 10 AWG              | Indoor/Outdoor            | Indoor                   |
| NEMA Configuration Code   | 5-20R                    | Operating Temperature     | -40°-60°C                |
| Wire Connection Type      | Internal Pressure Plates | Voltage                   | 125.0 V                  |
| Environmental Conditions  | Flammability: UL94 V2    |                           |                          |