



Pass and Seymour

20A 125V Heavy Duty Spec-Grade Tamper-Resistant Decorator Duplex Receptacle, Back and Side Wire, Red

Part No. TR26362RED

Tamper-Resistant Heavy-Duty Decorator Spec Grade Receptacles, Back and Side Wire, 20A, 125V



## Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects.

Auto-ground clip assures positive ground.

Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.

Backed-out tri-drive brass terminal screws for faster installation.

Internal screw-pressure-plate back and side wire capability.

Two back wire holes for additional wiring flexibility.

.032 inch thick brass triple-wipe power contacts.

Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

## Specifications

### General Info

|                       |                         |                    |                                                           |
|-----------------------|-------------------------|--------------------|-----------------------------------------------------------|
| Product Line          | Pass & Seymour          | Color              | Red                                                       |
| UPC Number            | 785007277371            | Country Of Origin  | Mexico                                                    |
| Number of Receptacles | 2                       | Features           | Decorator Style, Single Piece Plated Steel Mounting Strap |
| Outlet Type           | Tamper-Resistant        | Application Sector | Commercial                                                |
| Wall Plate Included   | No                      | Standard           | UL 498, FEDSPEC                                           |
| Warranty Type         | 1-Year Limited Warranty |                    |                                                           |

### Dimensions

|                   |          |                  |         |
|-------------------|----------|------------------|---------|
| Product Width US  | 1.322 in | Product Depth US | 0.78 in |
| Product Height US | 2.635 in |                  |         |

Listing Agencies / 3rd Party Agencies

|                     |         |              |     |
|---------------------|---------|--------------|-----|
| cULus ListingNumber | E140596 | cULus Listed | Yes |
|---------------------|---------|--------------|-----|

Technical Information

|                           |                 |                           |             |
|---------------------------|-----------------|---------------------------|-------------|
| Operating Temperature Min | -40 °C          | Is Tamper-Resistant       | Yes         |
| Connection Location       | Back and Side   | Phase                     | Three       |
| Number of Wires           | 3               | Operating Temperature Max | 60 °C       |
| Amperage                  | 20 A            | Number of Poles           | Double Pole |
| Wire Size                 | 14 - 10 AWG     | Indoor/Outdoor            | Indoor      |
| NEMA Configuration Code   | 5-20R           | Operating Temperature     | -40°-60°C   |
| Wire Connection Type      | Screw Terminals | Voltage                   | 125.0 V     |