



Pass and Seymour
Tamper-Resistant Extra Heavy Duty Surge Protective Duplex Receptacle, Light Almond
Part No. TR5262LASP



Tamper-Resistant Extra Heavy-Duty Surge Protective Duplex Receptacle offers increased transient protection, reliability and protection notification (Audible Alarm with LED Indicator). Back and Side Wire, 15amp 125volt, White. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects.

Auto-ground clip assures positive ground.

Backed-out tri-drive brass terminal screws for faster installation.

Internal screw-pressure-plate back and side wire capability.

Two back wire holes for additional wiring flexibility.

Corrosion-resistant plated steel strap is locked in to face and back body to resist pulling away from the face/body assembly.

.032 inch thick brass triple-wipe power contacts.

Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Light Almond
UPC Number	785007020465	Country Of Origin	China
Number of Receptacles	2	Features	Audible Alarm, Indicator Lights, Single Piece Plated Steel Mounting Strap, Surge Protection
Outlet Type	Straight Blade, Surge Protected, Tamper-Resistant	Application Sector	Commercial

Wall Plate Included	No	Warranty Type	1-Year Limited Warranty
Dimensions			
Product Width US	1.7 in	Product Depth US	1.4 in
Product Height US	2.75 in		
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		
Technical Information			
Is Tamper-Resistant	Yes	Connection Location	Back and Side
Phase	Single	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
NEMA Configuration Code	5-15R	Wire Connection Type	Screw Terminals
Voltage	125.0 V	Environmental Conditions	UL94 V2