



Pass and Seymour  
3.1A Spec Grade USB Outlet, Type A, 15A, Tamper-Resistant, Black  
Part No. TR5262USBBK



Designed for commercial markets with strength and durability in mind, this combination duplex receptacle and two USB Type-A features 3.1A overall USB charging capability and is compatible with USB 2.0 & 3.0 devices. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

## Features & Benefits

Overall 3.1A USB charging capability: Combination AC duplex receptacles include two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices.

Auto-ground clip assures positive ground.

AC receptacles are tamper-resistant as standard: patented shutter system prevents improper insertion of foreign objects.

Multiple color options available.

Back and side wire terminals accommodate #14 AWG - #10 AWG stranded and solid copper wire. Stainless steel auto-ground clips assure positive ground.

Wire Size: #14 - #10 AWG Copper Conductor Only

## Specifications

### General Info

|                    |                                                          |                       |                                |
|--------------------|----------------------------------------------------------|-----------------------|--------------------------------|
| Product Line       | Pass & Seymour                                           | Color                 | Black                          |
| Finish             | Matte                                                    | UPC Number            | 785007031690                   |
| Country Of Origin  | Vietnam                                                  | Number of Receptacles | 2                              |
| Features           | Single Piece Plated Steel Mounting Strap, USB-A Charging | Outlet Type           | Tamper-Resistant, USB-Charging |
| Application Sector | Commercial                                               | Wall Plate Included   | No                             |
| Standard           | CSA Listed, cULus, FSUL, UL Listed, RoHS, FEDSPEC        | Warranty Type         | 1-Year Limited Warranty        |

## Dimensions

|                                       |                          |                         |             |
|---------------------------------------|--------------------------|-------------------------|-------------|
| Product Width US                      | 1.693 in                 | Product Depth US        | 1.392 in    |
| Product Height US                     | 2.677 in                 |                         |             |
| Listing Agencies / 3rd Party Agencies |                          |                         |             |
| cULus ListingNumber                   | E140596                  | cULus Listed            | Yes         |
| Additional Information                |                          |                         |             |
| Product Environmental Profile         | Yes                      |                         |             |
| Technical Information                 |                          |                         |             |
| Dielectric Strength                   | Withstands 2000V minimum | Is Tamper-Resistant     | Yes         |
| Connection Location                   | Back and Side            | USB Wattage             | 15 W        |
| USB Amperage                          | 3.1 A                    | Number of USBs          | 2           |
| Number of Wires                       | 3                        | Amperage                | 15 A        |
| Number of Poles                       | Double Pole              | Wire Size               | 14 - 10 AWG |
| Indoor/Outdoor                        | Indoor                   | NEMA Configuration Code | 5-15R       |
| Wire Connection Type                  | Screw Terminals          | Voltage                 | 125.0 V     |