



Pass and Seymour  
3.1A Spec Grade USB Outlet, Type A, 20A, Tamper-Resistant, Red  
Part No. TR5362USBRED



Designed for commercial markets with strength and durability in mind, this combination USB charger duplex receptacle features 3.1A overall USB charging capability and is compatible with USB 2.0 & 3.0 devices. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

## Features & Benefits

Overall 3.1A USB charging capability: Combination AC duplex receptacles include two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices.

One-piece heat-treated triple-wipe brass power contacts.

AC receptacles are tamper-resistant as standard: patented shutter system prevents improper insertion of foreign objects.

Multiple color options available.

Back and side wire terminals accommodate #14 AWG - #10 AWG stranded and solid copper wire. Stainless steel auto-ground clips assure positive ground.

Wire Size: #14 - #10 AWG Copper Conductor Only

## Specifications

### General Info

|                       |                                                |                    |                                                   |
|-----------------------|------------------------------------------------|--------------------|---------------------------------------------------|
| Product Line          | Pass & Seymour                                 | Color              | Red                                               |
| UPC Number            | 785007031607                                   | Country Of Origin  | China                                             |
| Number of Receptacles | 2                                              | Features           | USB-A Charging                                    |
| Outlet Type           | Straight Blade, Tamper-Resistant, USB-Charging | Application Sector | Commercial                                        |
| Wall Plate Included   | No                                             | Standard           | CSA Listed, cULus, FSUL, UL Listed, RoHS, FEDSPEC |
| Warranty Type         | 1-Year Limited Warranty                        |                    |                                                   |

### Dimensions

|                                       |                                           |                           |                          |
|---------------------------------------|-------------------------------------------|---------------------------|--------------------------|
| Product Width US                      | 1.693 in                                  | Product Depth US          | 1.392 in                 |
| Product Height US                     | 2.677 in                                  |                           |                          |
| Listing Agencies / 3rd Party Agencies |                                           |                           |                          |
| cULus ListingNumber                   | E140596                                   | cULus Listed              | Yes                      |
| Additional Information                |                                           |                           |                          |
| Product Environmental Profile         | Yes                                       |                           |                          |
| Technical Information                 |                                           |                           |                          |
| Operating Temperature Min             | -40 °C                                    | Dielectric Strength       | Withstands 2000V minimum |
| Is Tamper-Resistant                   | Yes                                       | Connection Location       | Back and Side            |
| USB Wattage                           | 15 W                                      | USB Amperage              | 3.1 A                    |
| Phase                                 | Single                                    | Number of USBs            | 2                        |
| Number of Wires                       | 3                                         | Operating Temperature Max | 60 °C                    |
| Amperage                              | 20 A                                      | Number of Poles           | Double Pole              |
| Wire Size                             | 14 - 10 AWG                               | Indoor/Outdoor            | Indoor                   |
| NEMA Configuration Code               | 5-20R                                     | Operating Temperature     | -40°-60°C                |
| Wire Connection Type                  | Internal Pressure Plates, Screw Terminals | Voltage                   | 125.0 V                  |
| Environmental Conditions              | UL94 V2                                   |                           |                          |