



Pass and Seymour
Tamper-Resistant Hospital Grade Extra Heavy Duty Surge Protective Duplex Receptacle, Blue
Part No. TR8300BLSP



Tamper-Resistant Hospital Grade Extra Heavy-Duty Surge Protective Duplex Receptacle offers increased transient protection, reliability and protection notification (Audible Alarm with LED Indicator). Back and Side Wire, 20amp 125volt, Blue. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects.	Auto-ground clip assures positive ground.
Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.	Backed-out tri-drive brass terminal screws for faster installation.
Internal screw-pressure-plate back and side wire capability.	Two back wire holes for additional wiring flexibility.
Corrosion-resistant plated steel strap is locked in to face and back body to resist pulling away from the face/body assembly.	.032 inch thick brass triple-wipe power contacts.
Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.	For covering patents, see www.legrand.us/patents .

Specifications

General Info

Product Line	Pass & Seymour	Color	Blue
UPC Number	785007019421	Country Of Origin	China
Number of Receptacles	2	Features	Audible Alarm, Indicator Lights, Single Piece Plated Steel Mounting Strap, Surge Protection
Outlet Type	Hospital Grade, Tamper-Resistant	Application Sector	Commercial, Healthcare
Wall Plate Included	No	Warranty Type	1-Year Limited Warranty

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Is Tamper-Resistant	Yes	Connection Location	Back and Side
Phase	Single	Number of Wires	3
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
NEMA Configuration Code	5-20R	Wire Connection Type	Screw Terminals
Voltage	125.0 V	Environmental Conditions	UL94 V2