



Pass and Seymour  
**20A 125V Hospital-Grade Tamper-Resistant Compact Duplex Receptacle, Back and Side Wire, Red**  
Part No. TR8300HRED



Hospital-Grade Tamper-Resistant Compact Design Receptacle, Back and Side Wire, 20A, 125V

## Features & Benefits

Impact-resistant nylon face.

Stainless steel mounting screws also resist corrosion.

Easily accessible break-off line contact connecting tab for split circuit wiring.

Corrosion-resistant, zinc-plated steel strap is locked in.

Internal screw-pressure-plate back wire and side wire line terminals accept #14 : #10 AWG copper or copper-clad conductors.

High strength thermoplastic back body.

Compact design for easy installation.

Tri-drive terminal and mounting screws.

Meets National Electrical Code Tamper-Resistant requirements.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Wire Size: #14 - #10 AWG Copper Conductor Only

## Specifications

### General Info

|                    |                                          |                       |                                  |
|--------------------|------------------------------------------|-----------------------|----------------------------------|
| Product Line       | Pass & Seymour                           | Color                 | Red                              |
| Finish             | Matte                                    | UPC Number            | 785007035179                     |
| Country Of Origin  | Mexico                                   | Number of Receptacles | 2                                |
| Features           | Single Piece Plated Steel Mounting Strap | Outlet Type           | Hospital Grade, Tamper-Resistant |
| Application Sector | Commercial, Healthcare                   | Wall Plate Included   | No                               |
| Standard           | CSA Listed, UL Listed, FSUL              | Warranty Type         | 1-Year Limited Warranty          |

### Dimensions

|                  |          |                  |         |
|------------------|----------|------------------|---------|
| Product Width US | 1.322 in | Product Depth US | 0.78 in |
|------------------|----------|------------------|---------|

|                   |          |
|-------------------|----------|
| Product Height US | 2.635 in |
|-------------------|----------|

Listing Agencies / 3rd Party Agencies

|                     |         |              |     |
|---------------------|---------|--------------|-----|
| cULus ListingNumber | E140596 | cULus Listed | Yes |
|---------------------|---------|--------------|-----|

Technical Information

|                         |                          |                      |                 |
|-------------------------|--------------------------|----------------------|-----------------|
| Dielectric Strength     | Withstands 2000V minimum | Is Tamper-Resistant  | Yes             |
| Connection Location     | Back and Side            | Number of Wires      | 3               |
| Amperage                | 20 A                     | Number of Poles      | Double Pole     |
| Wire Size               | 14 - 10 AWG              | Indoor/Outdoor       | Indoor          |
| NEMA Configuration Code | 5-20R                    | Wire Connection Type | Screw Terminals |
| Voltage                 | 125.0 V                  |                      |                 |