



Pass and Seymour
3.1A Hospital Grade USB Outlet, Type A, 20A, Tamper-Resistant, White
Part No. TR8300HUSBW



Designed for the healthcare market and capable of withstanding heavy use due to its UL Hospital Grade certification. Features include an improved overall 3.1A USB charging capability, auto-ground clips, zinc-plated ground terminal screw, as well as triple-wipe brass contacts for lasting retention. The screw-pressure-plate back wiring makes installation fast and easy. Also available in black, green, gray, ivory, light almond, nickel, red and white. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

- Overall 3.1A USB charging capability: Combination AC duplex receptacles include two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices
- AC receptacles are tamper-resistant as standard: patented shutter system prevents improper insertion of foreign objects.
- Multiple color options available.
- Back and side wire terminals accommodate #14 AWG - #10 AWG stranded and solid copper wire.
- Stainless steel auto-ground clips assure positive ground.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007031560
Country Of Origin	Vietnam	Number of Receptacles	2
Features	Single Piece Plated Steel Mounting Strap, USB-A Charging	Outlet Type	Hospital Grade, Tamper-Resistant, USB-Charging
Application Sector	Commercial, Healthcare	Wall Plate Included	No
Standard	FEDSPEC	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	1.693 in	Product Depth US	1.392 in
Product Height US	2.677 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E140596	cULus Listed	Yes
Additional Information			
Product Environmental Profile	Yes		
Technical Information			
Operating Temperature Min	-40 °C	Is Tamper-Resistant	Yes
Connection Location	Back and Side	USB Wattage	15 W
USB Amperage	3.1 A	Number of USBs	2
Number of Wires	3	Operating Temperature Max	60 °C
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
NEMA Configuration Code	5-20R	Operating Temperature	-40°-60°C
Wire Connection Type	Internal Pressure Plates, Screw Terminals	Voltage	125.0 V