



Pass and Seymour  
**Tamper-Resistant Isolated Ground Decorator Hospital Grade Receptacle, Back and Side Wire, 15A, 125V, Red**  
Part No. TRIG26262HGRED



Tamper-Resistant Isolated Ground Decorator Hospital Grade Duplex Receptacle, Back and Side Wire, 15amp 125volt, White. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

## Features & Benefits

|                                                                                                                        |                                                                                                                                                                   |
|------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Corrosion-resistant, plated wraparound steel strap locked into assembly to prohibit strap from bending away from body. | One-piece, brass, triple-wipe power contacts for lasting retention.                                                                                               |
| Heavy-duty compact design for easier installation and long lasting performance.                                        | Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.                                                                       |
| Impact-resistant nylon face.                                                                                           | Terminal compartments isolated from each other for positive conductor containment.                                                                                |
| Side and internal screw-pressure-plate back wire accepts #14 : #10 AWG solid or stranded wire.                         | All devices fit standard #26 opening wall plate.                                                                                                                  |
| Tri-drive terminal and mounting screws.                                                                                | Auto-ground clip assures positive ground.                                                                                                                         |
| For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> .                         | For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, <a href="#">click here</a> . |

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

## Specifications

### General Info

|                       |                                                  |                    |                                                           |
|-----------------------|--------------------------------------------------|--------------------|-----------------------------------------------------------|
| Product Line          | Pass & Seymour                                   | Color              | Red                                                       |
| UPC Number            | 785007012330                                     | Country Of Origin  | Mexico                                                    |
| Number of Receptacles | 2                                                | Features           | Decorator Style, Single Piece Plated Steel Mounting Strap |
| Outlet Type           | Hospital Grade, Straight Blade, Tamper-Resistant | Application Sector | Commercial                                                |
| Wall Plate Included   | No                                               | Standard           | cULus UL498, FDSPEC                                       |

|                                       |                          |                          |                       |
|---------------------------------------|--------------------------|--------------------------|-----------------------|
| Warranty Type                         | 1-Year Limited Warranty  |                          |                       |
| Dimensions                            |                          |                          |                       |
| Product Width US                      | 1.187 in                 | Product Depth US         | 1.25 in               |
| Product Height US                     | 3.625 in                 |                          |                       |
| Listing Agencies / 3rd Party Agencies |                          |                          |                       |
| cULus ListingNumber                   | 140596                   | cULus Listed             | Yes                   |
| Technical Information                 |                          |                          |                       |
| Dielectric Strength                   | Withstands 2000V minimum | Is Tamper-Resistant      | Yes                   |
| Connection Location                   | Back and Side            | Number of Wires          | 3                     |
| Amperage                              | 15 A                     | Number of Poles          | Double Pole           |
| Wire Size                             | 14 - 10 AWG              | Indoor/Outdoor           | Indoor                |
| NEMA Configuration Code               | 5-15R                    | Wire Connection Type     | Screw Terminals       |
| Voltage                               | 125.0 V                  | Environmental Conditions | Flammability: UL94 V2 |