



Pass and Seymour
1-Gang Deep Extra Heavy Duty While-In-Use Cover, Gray/Clear
Part No. WIUCED10DCL



Extra Heavy-Duty While-In-Use Weatherproof Cover 1 Gang Deep

Features & Benefits

Comply with NEC 2014 Section 406.9 (B)(1) for wet location covers, and conforms to NEMA 3R.

Listed and identified as : Extra Duty: .

Covers are self closing as required by UL514C42.3.

Covers mount vertically and horizontally.

Body, cover, and plates are made of robust polycarbonate for added durability.

Mounting screws made of 302 stainless steel for corrosion resistance.

Single receptacle plate available in 1.405 inch and 1.595 inch openings.

Deep model available for 20A locking plugs.

Shallow covers accommodate up to 14/3 AWG extension cords.

New trigger latch opens easily with one finger.

Specifications

General Info

Product Line	Pass & Seymour	Color	Clear
Finish	Matte	UPC Number	785007320848
Country Of Origin	United States	Wall Plate Type	Custom
Application Sector	Commercial, Residential	Standard	cULus, CSA Listed, cURus, FSUL, UL Listed, RoHS
Warranty Type	1-Year Limited Warranty	Type	Wall Plate Accessories

Dimensions

Product Width US	5.34 in	Product Depth US	5.0 in
------------------	---------	------------------	--------

Product Height US	7.4 in
-------------------	--------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Number of Gangs	1	Indoor/Outdoor	Indoor
-----------------	---	----------------	--------

Number of Outlets	1
-------------------	---