



Pass and Seymour
1-Gang Deep Extra Heavy Duty While-In-Use Cover, Gray
Part No. WIUCED10GL



While-In-Use Weatherproof Cover 1 Gang

Features & Benefits

Comply with NEC 2005 Section 406.8(B)(1) for wet locations covers, and conforms to NEMA 3R.	Covers are self-closing as required by UL514C42.3.
Covers mount vertically or horizontally.	Body, cover, and plates made of polycarbonate.
Gasket made of closed cell foam, neoprene blend regular density, UL Rated HBF.	Mounting screws made of 302 stainless steel.
Single receptacle plate available in 1.405 inch and 1.595 inch openings.	Deep model available for 20A locking plugs.
Shallow covers accommodate up to 14/3 AWG extension cords.	New trigger latch opens easily with one finger.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Matte	UPC Number	785007320824
Country Of Origin	United States	Wall Plate Type	Custom
Application Sector	Commercial, Residential	Standard	cULus, CSA Listed, cURus, FSUL, UL Listed, RoHS
Warranty Type	1-Year Limited Warranty	Type	Wall Plate Accessories

Dimensions

Product Width US	5.34 in	Product Depth US	5.0 in
------------------	---------	------------------	--------

Product Height US	7.4 in
-------------------	--------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Number of Gangs	1	Indoor/Outdoor	Indoor
-----------------	---	----------------	--------

Number of Outlets	1
-------------------	---