



Pass and Seymour
2-Gang Extra Heavy Duty While-In-Use Cover, Gray/Clear
Part No. WIUCED20CL

Extra Heavy-Duty While-In-Use Weatherproof Cover,2 Gang



Features & Benefits

Comply with NEC 2014 Section 406.9 (B)(1) for wet location covers, and conforms to NEMA 3R.

Listed and identified as : Extra Duty: .

Covers are self closing as required by UL514C42.3.

Covers mount vertically and horizontally.

Body, cover, and plates are made of robust polycarbonate for added durability.

Mounting screws made of 302 stainless steel for corrosion resistance.

Single receptacle plate available in 1.405 inch and 1.595 inch openings.

Deep model available for 20A locking plugs.

Shallow covers accommodate up to 14/3 AWG extension cords.

New trigger latch opens easily with one finger.

Specifications

General Info

Product Line	Pass & Seymour	Color	Clear
UPC Number	785007320947	Country Of Origin	United States
Wall Plate Type	Custom	Application Sector	Commercial, Residential
Warranty Type	1-Year Limited Warranty	Type	Wall Plate Accessories

Dimensions

Product Width US	7.06 in	Product Depth US	4.0 in
Product Height US	7.71 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Number of Gangs	2	Indoor/Outdoor	Indoor
-----------------	---	----------------	--------

Number of Outlets	2
-------------------	---
