



Pass and Seymour
Weatherproof Single Gang Box, Gray
Part No. WPB26



Weatherproof 1 Gang Box, 5 Hole 1/2", 17.0 Cu.In., Gray (1 Hole Each End, 1 Hole Each Side, 1 Hole in Back)

Features & Benefits

Wide range of sizes, depths, and gangs.

Baked-on electrostatic, polyester, powder paint for superior scratch and corrosion resistance.

2 closure plugs and mounting lugs furnished with all boxes.

UL Listed for wet and/or damp locations with appropriate cover.

Designed for both interior and exterior applications.

Will accept standard 4 screw mounting covers and single gang weatherproof covers.

Simply strike desired knockout studs with a sharp hammer blow for clean mounting holes.

Heavy die-cast aluminum.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007116427	Country Of Origin	India
Material	Die-Cast Aluminum	Features	Corrosion Resistant, Weatherproof
Number of Knockouts	5	Application Sector	Commercial, Residential
Standard	UL listed	Warranty Type	1-Year Limited Warranty
Type	Weatherproof		

Dimensions

Product Width US	2.86 in	Product Weight US	0.62 lb
Product Volume US	17.0 cu in	Product Depth US	2.09 in
Product Height US	4.63 in	Product Length US	4.63 in
Cubic Capacity	17 in³	Box Depth	Shallow

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	143223
------------	-----	-----------------	--------

Technical Information

Number of Gangs	1	Size of Threaded Openings	1/2 in
Indoor/Outdoor	Both	Cable Entry	Back, Bottom, Side, Top
Box Shape	Rectangular	Mounting Type	Screw Mount