



Pass and Seymour
Weatherproof Two Gang Box, Gray
Part No. WPBD452



Weatherproof 2 Gang Deep Box, 5 Hole 1 37 Cu.In. with Threaded Holes, Gray (2 Holes Each End, 1 Hole in Back)

Features & Benefits

Baked-on electrostatic, polyester, powder paint for superior scratch and corrosion resistance.

4 closure plugs and mounting lugs furnished with all boxes.

UL listed for wet and/or damp locations with appropriate cover. Designed for both interior and exterior applications.

Will accept standard three-gang weatherproof covers.

Simply strike desired knockout studs with a sharp hammer blow for clean mounting holes.

Heavy die-cast aluminum.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007116052	Country Of Origin	India
Material	Die-Cast Aluminum	Features	Corrosion Resistant, Weatherproof
Number of Knockouts	3	Application Sector	Commercial, Residential
Standard	UL listed	Warranty Type	1-Year Limited Warranty
Type	Weatherproof		

Dimensions

Product Width US	4.5 in	Product Weight US	1.048 lb
Product Volume US	37.0 cu in	Product Depth US	2.72 in

Product Height US	4.5 in	Product Length US	4.5 in
Cubic Capacity	37 in³	Box Depth	Deep
Listing Agencies / 3rd Party Agencies			
CSA Listed	Yes	CSA File Number	143223
Technical Information			
Number of Gangs	2	Size of Threaded Openings	1 in
Indoor/Outdoor	Both	Cable Entry	Back, Bottom, Top
Box Shape	Square	Mounting Type	Screw Mount