



Pass and Seymour  
4-in Round Outdoor Cluster Cover, Gray  
Part No. WPRB13

Weatherproof 4-inch Round Outdoor Cluster Cover, Blank 3 Hole  
1/2-in With Gasket and Screws, Bronze



## Features & Benefits

Wide range of rectangular and round covers.

Baked-on electrostatic, polyester, powder paint for superior scratch and corrosion resistance.

Kits available combining fixtures, lamp covers, and accessories.

## Specifications

### General Info

|                   |                |                    |                                   |
|-------------------|----------------|--------------------|-----------------------------------|
| Product Line      | Pass & Seymour | Color              | Gray                              |
| Finish            | Matte          | UPC Number         | 785007117110                      |
| Country Of Origin | India          | Material           | Aluminum                          |
| Cover Type        | Weatherproof   | Features           | Corrosion Resistant, Weatherproof |
| Cover Shape       | Round          | Application Sector | Industrial                        |
| Standard          | UL listed      | Type               | Weatherproof Cover                |

### Dimensions

|                  |        |                   |         |
|------------------|--------|-------------------|---------|
| Product Width US | 4.0 in | Product Weight US | 0.36 lb |
| Product Depth US | 1.0 in |                   |         |

### Listing Agencies / 3rd Party Agencies

|            |     |                 |        |
|------------|-----|-----------------|--------|
| CSA Listed | Yes | CSA File Number | 164185 |
|------------|-----|-----------------|--------|

Technical Information

|                   |             |                    |            |
|-------------------|-------------|--------------------|------------|
| Number of Gangs   | 1           | Indoor/Outdoor     | Both       |
| Mounting Type     | Box Mounted | Box Cover Position | Horizontal |
| Number of Outlets | 3           |                    |            |