



Pass and Seymour
Wide Slide Series CFL/LED/Incandescent Single Pole Slide Dimmer, Preset, Tri-Color
Part No. WSCL450TC



Works with select dimmable CFL/LED or incandescent lighting loads and features a sleek, sculpted ergonomic design for smooth, easy operation and precise control.

Features & Benefits

Convenient Operation - Combines ON/OFF Decorator-style switch with separate slider for dimming control

Constant memory returns lights to previous level after a power failure

Sleek, ergonomic design that matches well with other decorator products

Higher ratings

Single-pole operation

Screw-pressure-plate back wire terminals save time, space and money

Rating: 450W LED & CFL: 700W Incandescent: 120VAC 60Hz

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory, Light Almond, White
Finish	Matte	UPC Number	785007040418
Country Of Origin	China	Material	Steel, Thermoplastic
Product Series	Decorator	Features	Color Change Kit
Switch Type	Slider	Number of Switches	1
Application Sector	Residential	Standard	cULus, RoHS
Warranty Type	Limited Lifetime Warranty		

Dimensions

Product Width US	1.75 in	Product Depth US	1.25 in
------------------	---------	------------------	---------

Product Height US	4.25 in
-------------------	---------

Technical Information

Preset	No	Load Rating	120V 450W (CFL), 120V 450W (LED), 120V 700W (Halogen), 120V 700W (Incandescent)
Dimming Compatibility	Forward Phase	Frequency Rating	60 Hz
Maximum Humidity	95% (relative humidity, non-condensing)	Number of Poles	Single Pole
Wire Size	#14 - #10 AWG	Requires Neutral Wire	No
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Wire Connection Type	Screw Terminals	Voltage	120 VAC
Load Type	CFL, Halogen, Incandescent, LED	Environmental Conditions	Humidity: Less than 95% non condensing