



Pass and Seymour
Wide Slide Preset Interchangeable Face Fan Speed Control, White
Part No. WSSC53PW



120V 5 Amp Wide Slide Preset Variable Speed Interchangeable Face Fan Speed Control. Simple to operate, this item comes with white face only (W).

Features & Benefits

Convenient operation - combines ON/OFF Decorator-style switch with separate slider for dimming control.

Constant memory returns lights to previous level after a power failure.

Sleek ergonomic P&S Decorator-style matches other Decorator devices.

Higher Ratings

Screw-pressure-plate back wire terminals save time, space and money.

This package is white face only option (W).

Interchangeable faces available in four colors -: Ivory,Brown,Black and Light Almond: (sold separately).

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007008852
Country Of Origin	China	Material	Steel, Thermoplastic
Features	Color Change Kit, Variable Speed Fan Control	Switch Type	Rocker, Slider
Number of Switches	1	Application Sector	Multi-Dwelling Unit, Residential
Warranty Type	Limited Lifetime Warranty	Type	Fan Speed Control

Dimensions

Product Width US	1.75 in	Product Depth US	1.25 in
------------------	---------	------------------	---------

Product Height US	4.25 in
-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Preset	Yes	Load Rating	120V 5A (Fan Control)
--------	-----	-------------	-----------------------

Dimming Compatibility	Fan Speed Only	Frequency Rating	60 Hz
-----------------------	----------------	------------------	-------

Number of Poles	3-Way, Single Pole	Wire Size	#14 - #12 AWG
-----------------	--------------------	-----------	---------------

Requires Neutral Wire	No	Indoor/Outdoor	Indoor
-----------------------	----	----------------	--------

Mounting Type	Wall Box	Wire Connection Type	Screw Terminals
---------------	----------	----------------------	-----------------

Voltage	120 VAC	Load Type	AC Fan Motor
---------	---------	-----------	--------------