



Pass and Seymour
Trademaster® 15A 125V Tamper-Resistant Duplex Receptacle, Ivory
Part No. 3232TRI



15A/125A Trademaster Registered Tamper-Resistant Duplex Receptacle

Features & Benefits

Quality Materials, durability, and time-tested design

Rated 15
amperes

Back and side wire termination options accepts #14–#10AWG solid & stranded wires, Copper-clad aluminum, and copper wire

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Matte	UPC Number	785007240184
Country Of Origin	China	Number of Receptacles	2
Outlet Type	Tamper-Resistant	Application Sector	Hospitality, Residential
Wall Plate Included	No	Standard	UL 498
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	1.32 in	Product Depth US	1.0 in
Product Height US	3.31 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Is Tamper-Resistant	Yes	Connection Location	Back and Side
Terminal Accommodation	#14 AWG - #10 AWG	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-15R
Wire Connection Type	Push Wire, Screw Terminals	Voltage	125.0 V