



15A/125A Weather-Resistant Duplex Receptacle,

### Features & Benefits

Quality Materials, durability, and time-tested design

Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.

Wire Size: #12 - #14 AWG, Solid wire

### Specifications

#### General Info

|                       |                                     |                         |                          |
|-----------------------|-------------------------------------|-------------------------|--------------------------|
| Product Line          | Pass & Seymour                      | Replaced by Part Number | 3232TREXWRW              |
| Color                 | White                               | Finish                  | Matte                    |
| UPC Number            | 785007241839                        | Country Of Origin       | Mexico                   |
| Number of Receptacles | 2                                   | Features                | Weatherproof             |
| Outlet Type           | Tamper-Resistant, Weather-Resistant | Application Sector      | Hospitality, Residential |
| Wall Plate Included   | No                                  | Standard                | UL 498                   |
| Warranty Type         | 1-Year Limited Warranty             |                         |                          |

#### Dimensions

|                   |         |                  |        |
|-------------------|---------|------------------|--------|
| Product Width US  | 1.32 in | Product Depth US | 1.0 in |
| Product Height US | 3.31 in |                  |        |

Listing Agencies / 3rd Party Agencies

|                     |         |              |     |
|---------------------|---------|--------------|-----|
| cULus ListingNumber | E140596 | cULus Listed | Yes |
|---------------------|---------|--------------|-----|

Additional Information

|                               |     |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

|                     |     |                     |           |
|---------------------|-----|---------------------|-----------|
| Is Tamper-Resistant | Yes | Connection Location | Side Only |
|---------------------|-----|---------------------|-----------|

|                 |   |          |      |
|-----------------|---|----------|------|
| Number of Wires | 3 | Amperage | 15 A |
|-----------------|---|----------|------|

|                 |             |           |             |
|-----------------|-------------|-----------|-------------|
| Number of Poles | Double Pole | Wire Size | 14 - 12 AWG |
|-----------------|-------------|-----------|-------------|

|                |         |                      |                               |
|----------------|---------|----------------------|-------------------------------|
| Indoor/Outdoor | Outdoor | Wire Connection Type | Push Wire, Screw<br>Terminals |
|----------------|---------|----------------------|-------------------------------|

|         |         |
|---------|---------|
| Voltage | 125.0 V |
|---------|---------|