



Pass and Seymour
30A 250V 6-30R Straight Blade Single Flush Receptacle, 2-Pole, 3-Wire
Part No. 3801



Straight Blade Receptacle 2-Pole 3-Wire 30A 250V

Features & Benefits

Quality Materials.

Durability.

Time-tested Design.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007380101	Country Of Origin	China
Number of Receptacles	1	Features	Durable
Outlet Type	Straight Blade	Application Sector	Multi-Dwelling Unit, Residential
Wall Plate Included	No	Standard	UL 498
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	2.5 in	Product Depth US	2.2 in
Product Height US	3.75 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus ListingNumber	140596
------------	-----	---------------------	--------

cULus Listed	Yes	CSA File Number	140596
--------------	-----	-----------------	--------

Technical Information

Number of Wires	3	Amperage	30 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor
NEMA Configuration Code	6-30	Voltage	250.0 V